







Stoni nosač za monitor  
**MH311**  
Uputstvo za upotrebu







Oznaka: MH311  
Proizvođač: Bestview Industry Limited  
Zemlja porekla: Kina  
Uvoznik za Srbiju: Elementa d.o.o.,  
Srbija, Subotica, Jovana Mikića 56  
Telefon: 024/686-270, www.elementa.rs




### KORAK 1A

#### Postavljanje baze (prenosna montaža)




### KORAK 1B


#### Postavljanje baze (fiksna montaža)



## KORAK 2 Postavljanje „ruke“ na bazu




## KORAK 3 Postavljanje monitora na nosač



## KORAK 4

Podešavanje zategnutosti opruge  
Podešavanje ugla monitora i fiksiranje kablova



NAPOMENA: Nakon stezanja provjerite da li se nosač podešava sa lakoćom.